

Specification Sheet

Part Number: 155-01600

Clip can be installed by hand – no need for hardware or tools.

Design provides low insertion and high extraction force, for simple, secure performance.

Clip keeps bundle away from areas that could cause damage due to rubbing.



Standoff Bundling Clip, 1.57" Long, 0.26 - 0.28" Mounting Hole, PA66HIRHS, Black 500/pkg

Article Number

155-01600

Type

STAND-OFF-CLIP-2

Color

Black (BK)

Quantity Per

pack

Product Description

Standoff bundling clips provide a straightforward way to secure cable bundles, hoses or pipes. The bundle fastens to the tape bar using tape or cable ties. Multiple orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standoff keeps bundles away from mounting area to prevent them from damage due to rubbing.

Short Description

Standoff Bundling Clip, 1.57" Long, 0.26 - 0.28" Mounting Hole, PA66HIRHS, Black 500/pkg

Global Part Name	STAND-OFF-CLIP-2-PA66HIRHS-BK
------------------	-------------------------------

Length L (Imperial)	1.57
---------------------	------

Length L (Metric)	40.0
-------------------	------

Offset Length (Imperial)	0.98
--------------------------	------

Offset Length (Metric)	25.0
------------------------	------

Fixation Method	Arrowhead
-----------------	-----------

Panel Thickness Min (Imperial)	0.02
--------------------------------	------

Panel Thickness Max (Imperial)	0.06
--------------------------------	------

Panel Thickness Min (Metric)	0.4
------------------------------	-----

Panel Thickness Max (Metric)	1.6
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.26 - 0.27 "
-------------------------------------	---------------

Mounting Hole Diameter D (Metric)	6.5 - 6.8 mm
-----------------------------------	--------------

Mounting Hole Diameter D Min (Imperial)	0.26
---	------

Mounting Hole Diameter D Max (Imperial)	0.27
---	------

Mounting Hole Diameter D Max (Metric)	6.8
---------------------------------------	-----

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com