

Specification Sheet

Part Number: 155-36002



HellermannTyton Connector Clips provide a single method to mount connectors to various surfaces in a variety of applications.

Highly engineered designs feature anti-rattle discs, anti-rotation oval fir trees and clamps for mounting on edges.

An assortment of Connector Clips is available to fit the variety of connector slot designs made by most of the largest global connector manufacturers.

Connector Clip with Round Fir Tree, 0.6 - 3.0 mm Panel Thick., 6.5 - 7.0 mm Hole Dia, PA66HIRHS, Black, 1000/pkg

Article Number	155-36002
----------------	-----------

Type	STECKERHALTER SITZ
------	--------------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
---------------------	---

Short Description	Connector Clip with Round Fir Tree, 0.6 - 3.0 mm Panel Thick., 6.5 - 7.0 mm Hole Dia, PA66HIRHS, Black, 1000/pkg
-------------------	--

Global Part Name	STECKERHALTER SITZ-PA66HIRHS-BK
------------------	---------------------------------

Length L (Imperial)	1.32
---------------------	------

Length L (Metric)	33.5
-------------------	------

Fixation Method	Fir tree for round holes
-----------------	--------------------------

Width W (Imperial)	0.4
--------------------	-----

Width W (Metric)	10.3
------------------	------

Height H (Imperial)	0.6
---------------------	-----

Height H (Metric)	15.2
-------------------	------

Panel Thickness Min (Imperial)	0.02
--------------------------------	------

Panel Thickness Max (Imperial)	0.12
--------------------------------	------

Panel Thickness Min (Metric)	0.6
------------------------------	-----

Panel Thickness Max (Metric)	3.0
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.26 - 0.28 "
-------------------------------------	---------------

Mounting Hole Diameter D (Metric)	6.5 - 7.0 mm 4.9 – 5.1 mm
-----------------------------------	---------------------------

Mounting Hole Diameter D Min (Imperial)	0.26
---	------

Mounting Hole Diameter D Max (Imperial)	0.28
---	------

Mounting Hole Diameter D Max (Metric) 7.0

Material Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut PA66HIRHS

Flammability UL 94 HB

UV Resistant (Yes/No) No

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 1000

Package Quantity (Metric) 1000

Customs Number 3926909988

