

Specification Sheet

Part Number: 156-00049



Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole

Edge Clip provides low insertion force and high extraction force ideal for assembly environments

Rotatable Cable Tie with Edge Clip, 6.3" Long, Outside Serrated, PA66HS, Black, 500/bg

Article Number	156-00049
----------------	-----------

Type	CBT30MR
------	---------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton's Two-Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place. The clips are available in 90° and 360° models for use with different types of cable tie. On the CBT30MR the bundle runs at the side of the clip and the cable tie is outside serrated to reduce bundle abrasion.
---------------------	--

Short Description	Rotatable Cable Tie with Edge Clip, 6.3" Long, Outside Serrated, PA66HS, Black, 500/bg
-------------------	--

Global Part Name	CBT30MR-PA66HS/POM-BK
------------------	-----------------------

Minimum Tensile Strength (Imperial)	30
-------------------------------------	----

Minimum Tensile Strength (Metric)	135
-----------------------------------	-----

Length L (Imperial)	6.3
---------------------	-----

Length L (Metric)	160
-------------------	-----

Fixation Method	Edge Clip
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.14
--------------------	------

Width W (Metric)	3.5
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.5
------------------------------	-----

Bundle Diameter Max (Imperial)	1.26
--------------------------------	------

Bundle Diameter Max (Metric)	32.0
------------------------------	------

Cable Tie Head Length (Imperial)	3.5
----------------------------------	-----

Height H (Imperial)	0.05
---------------------	------

Height H (Metric)	1.2
Cable Tie Width Max (Imperial)	0.14
Cable Tie Width Max (Metric)	3.5
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	2.5
Material	Polyacetal (POM) Polyamide 6.6 heat stabilized (PA66HS)
Foot Part Material	POM
Material Shortcut	PA66HS POM
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +194°F (-40°C to +90°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)