

Specification Sheet

Part Number: 156-01289

The 360 degree enclosure ensures the entire bundle is secure when being routed by this clip.

Locking tab on this clip is small enough that it will not interfere with any other portion of the wire routing, but is significant enough to allow for manual disengagement if service is needed.

The cable tie portion of this two-piece design allows for two wire bundles to be routed with the same piece.



LOC Locking Clamp, 5 - 9 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-01289
----------------	-----------

Type	T50RLOC5-9-SET
------	----------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The Locking Clip creates a full and secure lock completely around a wire bundle ranging from 10-14mm. The fixating fir tree on this clip allows for the clip to be secured into a panel by a 6mm round hole.
---------------------	--

Short Description	LOC Locking Clamp, 5 - 9 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 1000/ctn
-------------------	--

Global Part Name	T50RLOC5-9-SET-PA66HS/PA66HIRHSUV-BK
------------------	--------------------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	0.93
---------------------	------

Length L (Metric)	23.7
-------------------	------

Fixation Method	Omega Clip
-----------------	------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.47
--------------------	------

Width W (Metric)	12.0
------------------	------

Bundle Diameter Min (Imperial)	0.2
--------------------------------	-----

Bundle Diameter Min (Metric)	5.0
------------------------------	-----

Bundle Diameter Max (Imperial)	0.35
--------------------------------	------

Bundle Diameter Max (Metric)	9.0
------------------------------	-----

Height H (Imperial)	0.93
Height H (Metric)	23.6
Depth D (Imperial)	0.47
Depth D (Metric)	12.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to 105°C, +125C, 5000 h; 160C, 1000h; 165C, 500h per ITS 0019)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000

Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)