

Specification Sheet

Part Number: 156-01292

The 360 degree locking enclosure and cable tie dynamically fit a range of bundle sizes.

Clamp can be opened for bundle maintenance.

Low-profile release tab won't interfere with bundle or nearby routing.

The two bundles are allowed to rotate up to 90 degrees from one another.



LOC Locking Clamp, 15 - 19 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 1000/ctn

Article Number 156-01292

Type T50RLOC15-19-SET

Color Black (BK)

Quantity Per pack

Product Description The 2-Piece LOC with Saddle to T50R Tie has a two-piece design that keeps two routings secured together while providing a semi-fixed orientation for each bundle. The saddle design allows 90-degree rotation of the bundles. Tie provides additional security against axial slip by clamping around solid tube, pipe or harness.

Short Description LOC Locking Clamp, 15 - 19 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 1000/ctn

Global Part Name	T50RLOC15-19-SET-PA66HS/PA66HIRHSUV-BK
------------------	--

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	1.24
---------------------	------

Length L (Metric)	31.6
-------------------	------

Fixation Method	Omega Clip
-----------------	------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Bundle Diameter Min (Imperial)	0.59
--------------------------------	------

Bundle Diameter Min (Metric)	15.0
------------------------------	------

Bundle Diameter Max (Imperial)	0.75
--------------------------------	------

Bundle Diameter Max (Metric)	19.0
------------------------------	------

Height H (Imperial)	1.31
---------------------	------

Height H (Metric)	33.4
-------------------	------

Depth D (Imperial)	0.47
Depth D (Metric)	12.0
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HS PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)