

## Specification Sheet

Part Number: 156-01340



Bundle can rotate to any orientation, allowing routing in any direction regardless of mounting point.

2-piece design allows installer to slide clip around cable tie to obtain optimum orientation

Clip is reusable, making relocation or adjustments simple

1-Piece Cable Ties with Pipe Clip, 15-18mm, PA66HIRHS, Black, 500/pkg

|                |           |
|----------------|-----------|
| Article Number | 156-01340 |
|----------------|-----------|

|      |                |
|------|----------------|
| Type | T50SMVCOC15-18 |
|------|----------------|

|       |            |
|-------|------------|
| Color | Black (BK) |
|-------|------------|

|              |      |
|--------------|------|
| Quantity Per | pack |
|--------------|------|

|                     |                                                                                                                                                                                                                                                                                           |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | HellermannTyton's 1-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners. |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                   |                                                                       |
|-------------------|-----------------------------------------------------------------------|
| Short Description | 1-Piece Cable Ties with Pipe Clip, 15-18mm, PA66HIRHS, Black, 500/pkg |
|-------------------|-----------------------------------------------------------------------|

|                  |                                    |
|------------------|------------------------------------|
| Global Part Name | T50SMVCOC15-18-PA66HS/PA66HIRHS-BK |
|------------------|------------------------------------|

|                                     |                                                                                                            |
|-------------------------------------|------------------------------------------------------------------------------------------------------------|
| Minimum Tensile Strength (Imperial) | 50                                                                                                         |
| Minimum Tensile Strength (Metric)   | 222                                                                                                        |
| Length L (Imperial)                 | 8.3                                                                                                        |
| Length L (Metric)                   | 210.0                                                                                                      |
| Fixation Method                     | Omega Clip                                                                                                 |
| Identification Plate Position       | none                                                                                                       |
| Width W (Imperial)                  | 0.19                                                                                                       |
| Width W (Metric)                    | 4.7                                                                                                        |
| Bundle Diameter Min (Imperial)      | 0.08                                                                                                       |
| Bundle Diameter Min (Metric)        | 2.0                                                                                                        |
| Bundle Diameter Max (Imperial)      | 1.97                                                                                                       |
| Bundle Diameter Max (Metric)        | 50.0                                                                                                       |
| Material                            | Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)<br>Polyamide 6.6 heat stabilized (PA66HS) |
| Foot Part Material                  | PA66HIRHS                                                                                                  |

|                              |                                        |
|------------------------------|----------------------------------------|
| Material Shortcut            | PA66HS PA66HIRHS                       |
| Material Cable Tie           | Polyamide 6.6 heat stabilized (PA66HS) |
| Flammability                 | UL 94 HB                               |
| UV Resistant (Yes/No)        | No                                     |
| Use Conditions               | For Indoor and Outdoor Use             |
| Operating Temperature        | -40°F to +221°F (-40°C to +105°C)      |
| Reach Compliant (Article 33) | Yes                                    |
| ROHS Compliant               | Yes                                    |
| Package Quantity (Imperial)  | 500                                    |
| Package Quantity (Metric)    | 500                                    |
| Customs Number               | 3926909988                             |

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: corp@htamericas.com