

## Specification Sheet

Part Number: 156-01547

Versatile design allows cable routing above, perpendicular or parallel to stud.

Can mount up to three bundles simultaneously, making efficient use of a single mounting point.

Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure.



2-Piece M5/T5/M6/T6 Stud Mount Tie, 8.0" Tie, 50lb Tensile Strength, PA66HS/PA66HIRHS, BK, 3000/pkg

Article Number 156-01547

Type T50R0SBS5-6U-SET

Color Black (BK)

Quantity Per pack

Product Description Unique, two-piece design allows routing to be above, parallel or perpendicular to stud. This also enables up to three separate bundles to be fastened to the same stud. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.

Short Description 2-Piece M5/T5/M6/T6 Stud Mount Tie, 8.0" Tie, 50lb Tensile Strength, PA66HS/PA66HIRHS, BK, 3000/pkg

|                  |                                        |
|------------------|----------------------------------------|
| Global Part Name | T50R0SBS5-6U-SET-PA66HS/PA66HIRHSUV-BK |
|------------------|----------------------------------------|

|                                     |    |
|-------------------------------------|----|
| Minimum Tensile Strength (Imperial) | 50 |
|-------------------------------------|----|

|                                   |     |
|-----------------------------------|-----|
| Minimum Tensile Strength (Metric) | 222 |
|-----------------------------------|-----|

|                     |     |
|---------------------|-----|
| Length L (Imperial) | 8.0 |
|---------------------|-----|

|                   |       |
|-------------------|-------|
| Length L (Metric) | 202.0 |
|-------------------|-------|

|                 |            |
|-----------------|------------|
| Fixation Method | Stud Mount |
|-----------------|------------|

|                               |      |
|-------------------------------|------|
| Identification Plate Position | none |
|-------------------------------|------|

|                    |    |
|--------------------|----|
| Releasable Closure | No |
|--------------------|----|

|             |              |
|-------------|--------------|
| Tie Closure | plastic pawl |
|-------------|--------------|

|                    |       |
|--------------------|-------|
| Width W (Imperial) | 0.181 |
|--------------------|-------|

|                  |     |
|------------------|-----|
| Width W (Metric) | 4.6 |
|------------------|-----|

|                                |      |
|--------------------------------|------|
| Bundle Diameter Min (Imperial) | 0.16 |
|--------------------------------|------|

|                              |     |
|------------------------------|-----|
| Bundle Diameter Min (Metric) | 4.0 |
|------------------------------|-----|

|                                |      |
|--------------------------------|------|
| Bundle Diameter Max (Imperial) | 1.97 |
|--------------------------------|------|

|                              |      |
|------------------------------|------|
| Bundle Diameter Max (Metric) | 50.0 |
|------------------------------|------|

|            |           |
|------------|-----------|
| Cable Ties | 156-01547 |
|------------|-----------|

|                                         |                                                                                                                 |
|-----------------------------------------|-----------------------------------------------------------------------------------------------------------------|
| Height H (Imperial)                     | 0.74                                                                                                            |
| Height H (Metric)                       | 18.75                                                                                                           |
| Mounting Hole Diameter D (Imperial)     | 0.20 x 0.03"; 0.24 x 0.04"; 0.20                                                                                |
| Mounting Hole Diameter D (Metric)       | M6 x 1 T5 M5 x 0.8                                                                                              |
| Mounting Hole Diameter D Min (Imperial) | 0.2                                                                                                             |
| Mounting Hole Diameter D Max (Imperial) | 0.24                                                                                                            |
| Mounting Hole Diameter D Max (Metric)   | 6.0                                                                                                             |
| Stud Diameter (Metric)                  | 6.0 mm 5.0 mm                                                                                                   |
| Stud Diameter (Imperial)                | 0.20 ", 0.24                                                                                                    |
| Material                                | Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Foot Part Material                      | PA66HIRHS                                                                                                       |
| Material Shortcut                       | PA66HS PA66HIRHSUV                                                                                              |
| Material Cable Tie                      | Polyamide 6.6 heat stabilized (PA66HS)                                                                          |
| UV Resistant (Yes/No)                   | No                                                                                                              |
| Use Conditions                          | For Indoor and Outdoor Use                                                                                      |

|                              |                                   |
|------------------------------|-----------------------------------|
| Operating Temperature        | -40°F to +230°F (-40°C to +110°C) |
| Reach Compliant (Article 33) | Yes                               |
| ROHS Compliant               | Yes                               |
| Package Quantity (Imperial)  | 3000                              |
| Package Quantity (Metric)    | 3000                              |
| Customs Number               | 3926909988                        |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com