

Specification Sheet

Part Number: 156-01797

Low-profile clip attaches easily to plastic and metal edges as thin as 0.5 mm and up to 2.5 mm without the need for a mounting hole.

Two designs allow bundles to be secured parallel or vertical to surface edges.

Provides low insertion force and high extraction force – ideal for assembly environments.

Two-piece assembly allows the mount to slide along the strap, ensuring proper orientation.

Cable tie is outside serrated to reduce bundle chafing.



2-Piece Cable Tie with Edge Clip, 5.7"L, 0.5 - 2.5 mm Panel, Parallel, 30lb, PA66HS/PA66HIRHS, BK, 500/pkg

Article Number	156-01797
----------------	-----------

Type	T30ROSEC0.5-2.5SP-SVA
------	-----------------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.
---------------------	--

Short Description	2-Piece Cable Tie with Edge Clip, 5.7"L, 0.5 - 2.5 mm Panel, Parallel, 30lb, PA66HS/PA66HIRHS, BK, 500/pkg
Global Part Name	T30ROSEC0.5-2.5SP-SVA-PA66HS/PA66HIRHS-BK
Minimum Tensile Strength (Imperial)	30
Minimum Tensile Strength (Metric)	133
Length L (Imperial)	5.7
Length L (Metric)	145.0
Fixation Method	EdgeClip, sideways, assembled, 2 piece
Identification Plate Position	none
Variant	Outside Serrated
Width W (Imperial)	0.13
Width W (Metric)	3.4
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.6
Bundle Diameter Max (Imperial)	1.18
Bundle Diameter Max (Metric)	30
Height H (Imperial)	0.05

Height H (Metric)	1.2
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.10
Panel Thickness Min (Metric)	0.5
Panel Thickness Max (Metric)	2.5
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Foot Part Material	PA66HIRHS
Material Shortcut	PA66HIRHS PA66HS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Certification/Specification	UL ANSI/UL 62275
-----------------------------	--------------------

UL Recognized (US and Canada)	Yes
-------------------------------	-----

Package Quantity (Imperial)	500
-----------------------------	-----

Package Quantity (Metric)	500
---------------------------	-----

Customs Number	3926909988
----------------	------------

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)