

Specification Sheet

Part Number: 156-01922



Patented retention design of clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.

Clip and clamp both offer easy bundle installation.

Independent rotation allows for adjustable routing orientation.

Locking clamp dynamically fits a range of bundle sizes.

LOC Locking Clamp, 20-25 mm, to MOC Clip, 26 mm, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-01922
Type	MOC26FLOC20-25
Color	Black (BK)
Quantity Per	pack
Product Description	The MOC to LOC is a rotatable dual routing clip and clamp combination that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.
Short Description	LOC Locking Clamp, 20-25 mm, to MOC Clip, 26 mm, PA66HIRHSUV, Black, 1000/ctn
Global Part Name	MOC26FLOC20-25-PA66HIRHSUV-BK

Length L (Imperial)	2.87
Length L (Metric)	73.00
Variant	Clip to Clamp
Bundle Diameter Min (Imperial)	0.91
Bundle Diameter Min (Metric)	23.0
Bundle Diameter Max (Imperial)	1.14
Bundle Diameter Max (Metric)	29.0
Height H (Imperial)	1.61
Height H (Metric)	41.0
Depth D (Imperial)	0.47
Depth D (Metric)	12.0

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB

Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)