

Specification Sheet

Part Number: 156-02153



- Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.
- Controlled flex and angled entry promote easy installation.
- Independent rotation allows for adjustable routing orientation.

MOC Clip to MOC Clip Perpendicular, 19 mm, 7 mm Perpendicular, PA66HIRHSUV, Black, 2000/ctn

Article Number	156-02153
Type	MOC19FMOC7M180
Color	Black (BK)
Quantity Per	pack
Product Description	The MOC to MOC 180 is a rotatable dual routing clip that keeps two routings secured and separated. One clip is oriented 90 degrees from the other to provide alternative access for bundle attachment. A swivel coupler allows them to rotate independently of each other.
Short Description	MOC Clip to MOC Clip Perpendicular, 19 mm, 7 mm Perpendicular, PA66HIRHSUV, Black, 2000/ctn
Global Part Name	MOC19FMOC7M180-PA66HIRHSUV-BK

Length L (Imperial)	1.77
Length L (Metric)	44.84
Variant	Clip to Clip Transverse
Bundle Diameter Min (Imperial)	0.67
Bundle Diameter Min (Metric)	17.0
Bundle Diameter Max (Imperial)	0.86
Bundle Diameter Max (Metric)	21.8
Height H (Imperial)	1.29
Height H (Metric)	32.8
Depth D (Imperial)	0.47
Depth D (Metric)	12.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB

Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)