

Specification Sheet

Part Number: 156-02232

Versatile design allows cable routing above, perpendicular or parallel to stud.

Can mount up to three bundles simultaneously, making efficient use of a single mounting point.

Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure.



2-Piece M5/T5/M6/T6 Stud Mount Tie, 8.0" Tie, 50lb Tensile Strength, PPS/PAEK, SR/BGE, 3000/pkg

Article Number

156-02232

Type

PAT100LSBS5-6U2SET

Color

Beige (BGE) Silver (SR)

Quantity Per

pack

Product Description

Unique, two-piece design allows routing to be above, parallel or perpendicular to stud. This also enables up to three separate bundles to be fastened to the same stud. PA46 material option for high-temperature applications. This two-piece fastener offers the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications.

Short Description

2-Piece M5/T5/M6/T6 Stud Mount Tie, 8.0" Tie, 50lb Tensile Strength, PPS/PAEK, SR/BGE, 3000/pkg

Global Part Name	PAT100LSBS5-6U2SET-PPS/PAEK-BGE/SR
------------------	------------------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	223
-----------------------------------	-----

Length L (Imperial)	8.0
---------------------	-----

Length L (Metric)	203.2
-------------------	-------

Fixation Method	Stud Mount
-----------------	------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Width W (Imperial)	0.92
--------------------	------

Width W (Metric)	23.25
------------------	-------

Bundle Diameter Min (Imperial)	0.16
--------------------------------	------

Bundle Diameter Min (Metric)	4.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.97
--------------------------------	------

Bundle Diameter Max (Metric)	50.0
------------------------------	------

Cable Ties	156-02232
------------	-----------

Height H (Imperial)	0.74
Height H (Metric)	18.75
Mounting Hole Diameter D (Imperial)	0.20 x 0.03"; 0.24 x 0.04"; 0.20 "
Mounting Hole Diameter D (Metric)	M6 x 1 T5 M5 x 0.8
Mounting Hole Diameter D Min (Imperial)	0.2
Mounting Hole Diameter D Max (Imperial)	0.24
Mounting Hole Diameter D Max (Metric)	6.0
Stud Diameter (Metric)	6.0 mm 5.0 mm
Stud Diamater (Imperial)	0.20 ", 0.24
Material	Polyaryletherketone (PAEK) Polyphenylene Sulfide (PPS)
Foot Part Material	PAEK
Material Shortcut	PPS PAEK
Material Cable Tie	Polyaryletherketone (PAEK)
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use

Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)