

Specification Sheet

Part Number: 156-02273

5 mm offset shifts bundle away from adjacent panels.

Oval fir tree prevents bundle rotation.

HellermannTyton's 4x design provides best in-class installation and extraction resistance for four common oval sizes.

Secure into wide range of panel thicknesses up to 6.75 mm, for application versatility.



2-Piece Cable Tie with Oval Fir Tree Mount, 5mm Offset, 4x Oval Hole FT, PA66HIRHSUV, Black, 3000/ctn

Article Number

156-02273

Type

T50ROSSADFTOVALSET

Color

Black (BK)

Quantity Per

pack

Product Description

These two-piece fasteners are pre-assembled and offer a simple and versatile method of bundling and mounting cables. Sold as an unassembled set, this oval fir tree and tie combination allows the user to install the tie in two different directions, securing the bundle perpendicular or inline to the oval mounting hole.

Short Description

2-Piece Cable Tie with Oval Fir Tree Mount, 5mm Offset, 4x Oval Hole FT, PA66HIRHSUV, Black, 3000/ctn

Global Part Name	T50ROSSADFTOVALSET-PA66HIRHSUV-BK
------------------	-----------------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Fixation Method	Fir Tree for oval holes
-----------------	-------------------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Bundle Diameter Min (Imperial)	0.08
--------------------------------	------

Bundle Diameter Min (Metric)	2.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.97
--------------------------------	------

Bundle Diameter Max (Metric)	50.0
------------------------------	------

Panel Thickness Min (Imperial)	0.02
--------------------------------	------

Panel Thickness Max (Imperial)	0.27
--------------------------------	------

Panel Thickness Min (Metric)	0.6
------------------------------	-----

Panel Thickness Max (Metric)	6.75
------------------------------	------

Mounting Hole Diameter D (Imperial)	0.24 x 0.48 " 0.26 x 0.49 " 0.26 x 0.51 " 0.28 x 0.47 "
Mounting Hole Diameter D (Metric)	6.5 x 13.0 mm 6.2 x 12.2 mm 7.0 x 12.0 mm 6.5 x 12.5 mm
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)