

Specification Sheet

Part Number: 156-02384



Bundle can rotate to any orientation, allowing routing in any direction regardless of mounting point.

Clip is reusable, making relocation or adjustments simple.

All-in-one bundling and mounting solution reduces costs.

LOC Locking Clamp, 5 - 9 mm, with T50SMVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn

|                     |                                                                                                                                                                                                                                                                                           |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 156-02384                                                                                                                                                                                                                                                                                 |
| Type                | T50SMVCLOC5-9                                                                                                                                                                                                                                                                             |
| Color               | Black (BK)                                                                                                                                                                                                                                                                                |
| Quantity Per        | pack                                                                                                                                                                                                                                                                                      |
| Product Description | HellermannTyton's 1-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners. |
| Short Description   | LOC Locking Clamp, 5 - 9 mm, with T50SMVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn                                                                                                                                                                                                        |
| Global Part Name    | T50SMVCLOC5-9-PA66HIRHSUV-BK                                                                                                                                                                                                                                                              |

|                                     |            |
|-------------------------------------|------------|
| Minimum Tensile Strength (Imperial) | 50         |
| Minimum Tensile Strength (Metric)   | 225        |
| Length L (Imperial)                 | 8.3        |
| Length L (Metric)                   | 210.0      |
| Fixation Method                     | Omega Clip |
| Identification Plate Position       | none       |
| Width W (Imperial)                  | 0.47       |
| Width W (Metric)                    | 12.0       |
| Bundle Diameter Min (Imperial)      | 0.2        |
| Bundle Diameter Min (Metric)        | 5.0        |
| Bundle Diameter Max (Imperial)      | 0.35       |
| Bundle Diameter Max (Metric)        | 9.0        |
| Height H (Imperial)                 | 1.08       |
| Height H (Metric)                   | 23.6       |
| Depth D (Imperial)                  | 0.47       |
| Depth D (Metric)                    | 12.0       |

|                                         |                                                                          |
|-----------------------------------------|--------------------------------------------------------------------------|
| Mounting Hole Diameter D (Imperial)     | 0.2 - 0.35                                                               |
| Mounting Hole Diameter D (Metric)       | 5.0 - 9.0 mm                                                             |
| Mounting Hole Diameter D Min (Imperial) | 0.2                                                                      |
| Mounting Hole Diameter D Max (Imperial) | 0.35                                                                     |
| Mounting Hole Diameter D Max (Metric)   | 9.0                                                                      |
| Material                                | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Foot Part Material                      | PA66HIRHS                                                                |
| Material Shortcut                       | PA66HIRHSUV                                                              |
| Material Cable Tie                      | Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)         |
| Flammability                            | UL 94 HB                                                                 |
| Halogen Free                            | Yes                                                                      |
| UV Resistant (Yes/No)                   | Yes                                                                      |
| Use Conditions                          | For Indoor and Outdoor Use                                               |
| Operating Temperature                   | -40°F to +221°F (-40°C to +105°C)                                        |
| Reach Compliant (Article 33)            | Yes                                                                      |

|                             |            |
|-----------------------------|------------|
| ROHS Compliant              | Yes        |
| Package Quantity (Imperial) | 1000       |
| Package Quantity (Metric)   | 1000       |
| Customs Number              | 3926909988 |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)