

Specification Sheet

Part Number: 156-02517



Friction tab inside the fir tree allows the tie to sit in mount without falling out prior to installation

Fir tree provides low insertion effort yet demonstrates high extraction resistance

Disc feature prevents rattling in high-vibration applications and protects against debris ingress

2-Piece Cable Tie with Fir Tree Mount, 8.0"L, 0.024 - 0.138" Panel Thickness, PA66HIRHSUV, Black, 5000/ctn

Article Number	156-02517
Type	T50RFT6ASET
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold unassembled with the cable tie.
Short Description	2-Piece Cable Tie with Fir Tree Mount, 8.0"L, 0.024 - 0.138" Panel Thickness, PA66HIRHSUV, Black, 5000/ctn

Global Part Name	T50RFT6ASET-PA66HIRHSUV-BK
------------------	----------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	8.0
---------------------	-----

Length L (Metric)	203.2
-------------------	-------

Fixation Method	Fir tree for round holes
-----------------	--------------------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.63
--------------------	------

Width W (Metric)	16.0
------------------	------

Bundle Diameter Min (Imperial)	0.08
--------------------------------	------

Bundle Diameter Min (Metric)	2.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.97
--------------------------------	------

Bundle Diameter Max (Metric)	50.0
------------------------------	------

Height H (Imperial)	0.65
Height H (Metric)	16.4
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.14
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	3.5
Mounting Hole Diameter D (Imperial)	0.24 - 0.28
Mounting Hole Diameter D (Metric)	6.1 - 7.1 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.28
Mounting Hole Diameter D Max (Metric)	7.1
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Foot Part Material	PA66HIRHSUV
Material Shortcut	PA66HIRHSUV
Material Cable Tie	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	5000
Package Quantity (Metric)	5000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)