

Specification Sheet

Part Number: 156-02883

- MOC stud mount secures bundles above a bolt or stud.
- Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.
- Controlled flex and angled entry promote easy installation.
- Independent rotation allows for adjustable routing orientation.
- High-performance stud mount design allows for easy installation and delivers outstanding stud retention to keep bundles secure.



Stud Mount to MOC Clip, 19mm Clip Above Mount, 5mm/6mm Stud Mount, PA66HIRHSUV, Black, 2000/ctn

Article Number	156-02883
Type	SMFMOC19M
Color	Black (BK)
Quantity Per	pack
Product Description	The MOC with stud mount features HellermannTyton's unique retention clip with a best-in-class stud mount to secure to a 5mm or 6mm stud or bolt. The mount delivers a low insertion force while exhibiting high extraction resistance for a secure mounting point.

Short Description	Stud Mount to MOC Clip, 19mm Clip Above Mount, 5mm/6mm Stud Mount, PA66HIRHSUV, Black, 2000/ctn
Global Part Name	SMFMOC19M-PA66HIRHSUV-BK
Length L (Imperial)	1.29
Length L (Metric)	32.8
Fixation Method	Stud Mount
Bundle Diameter Min (Imperial)	0.67
Bundle Diameter Min (Metric)	17.0
Bundle Diameter Max (Imperial)	0.86
Bundle Diameter Max (Metric)	21.8
Height H (Imperial)	1.91
Height H (Metric)	48.6
Depth D (Imperial)	0.59
Depth D (Metric)	15.0
Nominal Diameter (Metric)	19.0
Stud Diameter (Metric)	5.0 mm 6.0 mm
Stud Diamater (Imperial)	0.20 ";0.24

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com