

Specification Sheet

Part Number: 156-00538



Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.

Edge Clip provides low insertion force and high extraction force ideal for assembly environments.

2-Piece Cable Tie with Edge Clip, 8.0" Long, EC4B, 1 - 3 mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/pkg

Article Number 156-00538

Type T50REC4B

Color Black (BK)

Quantity Per pack

Product Description HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

Short Description 2-Piece Cable Tie with Edge Clip, 8.0" Long, EC4B, 1 - 3 mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/pkg

Global Part Name T50REC4B-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.0
Length L (Metric)	202.0
Fixation Method	Edge Clip
Identification Plate Position	none
Releasable Closure	No
Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.16
Bundle Diameter Min (Metric)	4.0
Bundle Diameter Max (Imperial)	1.77
Bundle Diameter Max (Metric)	45.0
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2

Height H (Imperial)	0.63
Height H (Metric)	16.0
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)
Foot Part Material	PA66HIRHSUV
Material Shortcut	PA66HS PA66HIRHS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C) -40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)