

Specification Sheet

Part Number: 156-01843



Patented retention design of clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.

Clip and clamp both offer easy bundle installation.

Independent rotation allows for adjustable routing orientation.

Locking clamp dynamically fits a range of bundle sizes.

LOC Locking Clamp, 5-9 mm, to MOC Clip, 16 mm, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-01843
Type	MOC16FLOC5-9
Color	Black (BK)
Quantity Per	pack
Product Description	The MOC to LOC is a rotatable dual routing clip and clamp combination that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.
Short Description	LOC Locking Clamp, 5-9 mm, to MOC Clip, 16 mm, PA66HIRHSUV, Black, 1000/ctn
Global Part Name	MOC16FLOC5-9-PA66HIRHSUV-BK

Length L (Imperial)	1.85
Length L (Metric)	47.10
Variant	Clip to Clamp
Bundle Diameter Min (Imperial)	0.55
Bundle Diameter Min (Metric)	14.0
Bundle Diameter Max (Imperial)	0.72
Bundle Diameter Max (Metric)	18.3
Height H (Imperial)	1.01
Height H (Metric)	25.7
Depth D (Imperial)	0.47
Depth D (Metric)	12.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB

Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com