

Specification Sheet

Part Number: 156-01853



Patented retention design of clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.

Clip and clamp both offer easy bundle installation.

Independent rotation allows for adjustable routing orientation.

Locking clamp dynamically fits a range of bundle sizes.

Article Number	156-01853
Type	MOC6FLOC10-14
Color	Black (BK)
Quantity Per	pack
Product Description	The MOC to LOC is a rotatable dual routing clip and clamp combination that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.
Short Description	LOC Locking Clamp, 10-14 mm, to MOC Clip, 6 mm, PA66HIRHSUV, Black, 2500/ctn
Global Part Name	MOC6FLOC10-14-PA66HIRHSUV-BK

Length L (Imperial)	1.59
Length L (Metric)	40.40
Variant	Clip to Clamp
Bundle Diameter Min (Imperial)	0.22
Bundle Diameter Min (Metric)	5.5
Bundle Diameter Max (Imperial)	0.27
Bundle Diameter Max (Metric)	6.8
Height H (Imperial)	1.08
Height H (Metric)	27.4
Depth D (Imperial)	0.47
Depth D (Metric)	12.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes

UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2500
Package Quantity (Metric)	2500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)