

Specification Sheet

Part Number: 156-02324



Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.

Controlled flex and angled entry promote easy installation.

Independent rotation allows for adjustable routing orientation.

MOC Clip to MOC Clip, 8 mm, 26 mm, PA66HIRHSUV, Black, 2000/ctn

Article Number 156-02324

Type MOC8FMOC26M

Color Black (BK)

Quantity Per pack

Product Description The MOC to MOC is a rotatable dual routing clip that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

Short Description MOC Clip to MOC Clip, 8 mm, 26 mm, PA66HIRHSUV, Black, 2000/ctn

Global Part Name MOC8FMOC26M-PA66HIRHSUV-BK

Length L (Imperial)	2.08
Length L (Metric)	52.8
Variant	Clip to Clip
Bundle Diameter Min (Imperial)	0.28
Bundle Diameter Min (Metric)	7.0
Bundle Diameter Max (Imperial)	0.35
Bundle Diameter Max (Metric)	9.0
Height H (Imperial)	1.61
Height H (Metric)	41.0
Depth D (Imperial)	0.47
Depth D (Metric)	12.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes

UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com