

## Specification Sheet

Part Number: 156-03002

Clamp and mount combination means no extra hardware is needed, for time-saving, toolless, one-handed installation.

Three size ranges handle diameters from 0.5" to 2", reducing part inventory.

Clamp saddle provides additional attachment option using a cable tie.

Impact modified, heat and UV stabilized PA66 provides long-term durability, indoors and out.



Quick2Clamp, Ratchet, 0.76" - 1.42" Bundle Dia, 1-5/8" Strut Attachment, PA66HIRHSUV, Black, 200/box

|                |           |
|----------------|-----------|
| Article Number | 156-03002 |
|----------------|-----------|

|      |           |
|------|-----------|
| Type | IRCCSTRUT |
|------|-----------|

|       |            |
|-------|------------|
| Color | Black (BK) |
|-------|------------|

|              |      |
|--------------|------|
| Quantity Per | pack |
|--------------|------|

|                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | <p>The Quick2Clamp offers ultra-fast installation and versatility for managing conduit, tubing and cables. The built-in strut mount attaches with a simple twist. The one-piece design makes it simple to install without tools. Robust, adjustable clamp closes by hand to the desired diameter. A release feature allows easy and nondestructive maintenance simply by using a flat-head screwdriver. In this way, the clamp can be reused or serviced without removing it from the strut.</p> |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                                |                                                                                                      |
|--------------------------------|------------------------------------------------------------------------------------------------------|
| Short Description              | Quick2Clamp, Ratchet, 0.76" - 1.42" Bundle Dia, 1-5/8" Strut Attachment, PA66HIRHSUV, Black, 200/box |
| Global Part Name               | IRCCSTRUT-PA66HIRHSUV-BK                                                                             |
| Length L (Imperial)            | 4.56                                                                                                 |
| Length L (Metric)              | 115.9                                                                                                |
| Fixation Method                | 1-5/8 " Strut Attachment                                                                             |
| Variant                        | Load Rating: 17 lbs, Safety Factor: 3 Pull Force Rating: 50 lbs                                      |
| Width W (Imperial)             | 1.37                                                                                                 |
| Width W (Metric)               | 34.81                                                                                                |
| Bundle Diameter Min (Imperial) | 0.76                                                                                                 |
| Bundle Diameter Min (Metric)   | 19.4                                                                                                 |
| Bundle Diameter Max (Imperial) | 1.42                                                                                                 |
| Bundle Diameter Max (Metric)   | 36.0                                                                                                 |
| Height H (Imperial)            | 2.04                                                                                                 |
| Height H (Metric)              | 51.8                                                                                                 |

|                              |                                                                          |
|------------------------------|--------------------------------------------------------------------------|
| Material                     | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Material Shortcut            | PA66HIRHSUV                                                              |
| Halogen Free                 | Yes                                                                      |
| UV Resistant (Yes/No)        | Yes                                                                      |
| Use Conditions               | For Indoor and Outdoor Use                                               |
| Operating Temperature        | -40°F to +221°F (-40°C to +105°C)                                        |
| Reach Compliant (Article 33) | Yes                                                                      |
| ROHS Compliant               | Yes                                                                      |
| Certification/Specification  | UL   UL2239 Conduit & Cable Hanger                                       |
| UL Listed (US)               | Yes                                                                      |
| Package Quantity (Imperial)  | 200                                                                      |
| Package Quantity (Metric)    | 200                                                                      |
| Customs Number               | 3926909988                                                               |

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.