

Specification Sheet

Part Number: 156-03233

No drilling or extra hardware required – just secure to steel surface.

Magnetic mounts are reliable even in debris, dirt, and oil.

Use for permanent mounting or as a temporary installation tool.

Reuse and reposition capabilities allow for a flexible mounting solution.

Easily remove without residue.



Article Number	156-03233
Type	T50RMAGCTM15LSET
Color	Black (BK)
Quantity Per	pack
Product Description	Magnetic cable tie mount with T50R tie routes bundles by securing to steel surfaces without the need for a mounting hole. Simply attach the wire bundle to the mount with the cable tie and position it onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. The mounts are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts.

Short Description	2-Piece Cable Tie/Magnet Mount, Unassembled Set, 0.91" Dia, Magnet/POM/ST, 15lb Pull, Black, 100/Box
Global Part Name	T50RMAGCTM15LSET-NDFEB35M/POM/ST/PA66HS-BK
Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	222
Fixation Method	Magnet
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Bundle Diameter Min (Imperial)	0.2
Bundle Diameter Min (Metric)	5
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50
Thickness T (Imperial)	0.047
Thickness T (Metric)	1.2
Height H (Imperial)	0.41
Height H (Metric)	10.5

Diameter D (Imperial)	0.91
Diameter D (Metric)	23.2
Cable Tie Width Max (Imperial)	0.23
Cable Tie Width Max (Metric)	5.9
Material	Polyacetal (POM) Polyamide 6.6 heat stabilized (PA66HS) Steel (ST) Neodymium alloy 35M (NDFEB35M)
Material Shortcut	ST POM PA66HS NDFEB35M
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Halogen Free	Yes
Plenum Rating	AH-2
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100

Customs Number

8505110070

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)