

Specification Sheet

Part Number: 157-00329

Delivers high extraction force for reliable performance, yet it's easy to install.

Reusable fastener can be removed from threaded or nonthreaded holes using a 5/16" hex driver.

Heat stabilized material provides excellent resistance to high temperatures.



Blind Hole Mount Cable Tie, Offset, 8"L, 0.25" Thread/Non-Thread Hole, 50lb, PA66HS, Black, 500/bg

Article Number	157-00329
Type	T50ROSBHMBSO18
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton Blind Hole Mount Cable Ties for threaded and nonthreaded holes offer an easy-to-use method for bundling and affixing cables. The 2-piece design includes a heat stabilized cable tie and formula-matched, 1/4" mount that features a low insertion force and aggressively resists pull off. Performs equally well in threaded or nonthreaded blind holes. Mount can slide along cable tie to adjust orientation if needed. Fastener can be removed from hole using a hex driver. This ensures fastener can be reused.
Short Description	Blind Hole Mount Cable Tie, Offset, 8"L, 0.25" Thread/Non-Thread Hole, 50lb, PA66HS, Black, 500/bg

Global Part Name	T50ROSBHMBSO18-PA66HS-BK
------------------	--------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	8.0
---------------------	-----

Length L (Metric)	203.2
-------------------	-------

Offset Length (Imperial)	0.71
--------------------------	------

Offset Length (Metric)	18.0
------------------------	------

Fixation Method	Blind Plug
-----------------	------------

Identification Plate Position	none
-------------------------------	------

Width W (Imperial)	0.185
--------------------	-------

Width W (Metric)	4.7
------------------	-----

Bundle Diameter Min (Imperial)	0.08
--------------------------------	------

Bundle Diameter Min (Metric)	2.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.97
--------------------------------	------

Bundle Diameter Max (Metric)	50.0
------------------------------	------

Height H (Imperial)	0.736
---------------------	-------

Height H (Metric)	18.7
Diameter D (Imperial)	0.25
Diameter D (Metric)	6.35
Mounting Hole Diameter D (Imperial)	0.246 - 0.253
Mounting Hole Diameter D (Metric)	6.25 - 6.45 mm
Mounting Hole Diameter D Min (Imperial)	0.25
Mounting Hole Diameter D Max (Imperial)	0.25
Mounting Hole Diameter D Max (Metric)	6.45

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +257°F (-40°C to +125°C)

Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)