

Specification Sheet

Part Number: 157-00335



Offset design positions bundles away from obstructions, heat or sources of abrasion.

Low profile head allows mounts to stack, providing more mounting versatility from a single stud.

Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure.

Offset Low-Profile Stud Mount Tie, 7.5" Tie, 50lb Tensile Strength, PA66HIRHSUV, Black, 3000/pkg

Article Number	157-00335
Type	T50ROSLPM6SMSO25
Color	Black (BK)
Quantity Per	pack
Product Description	One-piece cable tie with stud mount features an offset design to position bundles away from obstructions, heat or sources of abrasion. It includes a low-profile head, allowing multiple tie mounts to be stacked on a single bolt and providing space savings in tight areas. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.

Short Description	Offset Low-Profile Stud Mount Tie, 7.5" Tie, 50lb Tensile Strength, PA66HIRHSUV, Black, 3000/pkg
Global Part Name	T50ROSLPM6SMSO25-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.8
Length L (Metric)	223.52
Offset Length (Imperial)	1.0
Offset Length (Metric)	25.5
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.56
Width W (Metric)	14.2
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0

Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Cable Ties	157-00335
Height H (Imperial)	0.25
Height H (Metric)	6.30
Mounting Hole Diameter D (Imperial)	0.24 x 0.04 "
Mounting Hole Diameter D (Metric)	M6 x 1
Stud Diameter (Metric)	5.0 mm 6.0 mm
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)