

Specification Sheet

Part Number: 157-00144



One-piece design allows installers to mount and bundle wire or cables single-handedly.

Fastener delivers high extraction force for reliable performance, yet it's easy to install.

Can be unscrewed or extracted from threaded holes for easy removal and re-usability.

1-Piece Cable Tie with Fir Tree Mount with Disc, 8"L, M6 Threaded Hole, PA46, Brown, 500/pkg

Article Number	157-00144
Type	T50ROSFTQM6
Color	Brown (BN)
Quantity Per	pack
Product Description	HellermannTyton Blind Hole Mount Cable Tie for threaded holes offers an easy-to-use method for bundling and affixing cables. The one-piece mount offers a low insertion force and aggressively resists pull off, for secure attachment to panel holes with thicknesses from 0.02" to 0.28" or threaded blind holes. The disc on top of the mount covers the hole and minimizes ingress of water and debris.
Short Description	1-Piece Cable Tie with Fir Tree Mount with Disc, 8"L, M6 Threaded Hole, PA46, Brown, 500/pkg

Global Part Name	T50ROSFTQM6-PA46-BN
------------------	---------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	8.0
---------------------	-----

Length L (Metric)	203.2
-------------------	-------

Fixation Method	Fir tree for round holes
-----------------	--------------------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Width W (Imperial)	0.2
--------------------	-----

Width W (Metric)	5.08
------------------	------

Bundle Diameter Min (Imperial)	0.08
--------------------------------	------

Bundle Diameter Min (Metric)	2.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.97
--------------------------------	------

Bundle Diameter Max (Metric)	50.0
------------------------------	------

Thickness T (Imperial)	0.06
------------------------	------

Thickness T (Metric)	1.5
Height H (Imperial)	0.54
Height H (Metric)	13.8
Diameter D (Imperial)	0.25
Diameter D (Metric)	6.0
Panel Thickness Min (Imperial)	0.13
Panel Thickness Max (Imperial)	0.28
Panel Thickness Min (Metric)	3.25
Panel Thickness Max (Metric)	7.0
Mounting Hole Diameter D (Metric)	M6
Disc Diameter (Metric)	15.88
Disc Diameter (Imperial)	0.66
Material	Polyamide 4.6 (PA46)
Material Shortcut	PA46
Flammability	UL 94 HB

UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +266°F (-40°C to +130°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)