

Specification Sheet

Part Number: 157-00294

Covers top of stud for protection from stud end.

Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure.

PA46 material option allows use in high-heat applications.



M10 Stud Mount Tie, 7.5" Tie, 80lb Tensile Strength, PA46, Brown, 2000/pkg

Article Number	157-00294
----------------	-----------

Type	T80ROSSB10U
------	-------------

Color	Brown (BN)
-------	------------

Quantity Per	pack
--------------	------

Product Description	These mounts offer outstanding stud retention. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.
---------------------	---

Short Description	M10 Stud Mount Tie, 7.5" Tie, 80lb Tensile Strength, PA46, Brown, 2000/pkg
-------------------	--

Global Part Name	T80ROSSB10U-PA46-BN
------------------	---------------------

Minimum Tensile Strength (Imperial)	80
Minimum Tensile Strength (Metric)	335
Length L (Imperial)	8.5
Length L (Metric)	215.0
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.22
Width W (Metric)	10.0
Bundle Diameter Min (Imperial)	0.14
Bundle Diameter Min (Metric)	3.5
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Cable Ties	157-00294
Height H (Imperial)	0.59

Height H (Metric)	15.0
Mounting Hole Diameter D (Imperial)	0.39 x 0.06 "
Mounting Hole Diameter D (Metric)	M10 x 1.5
Stud Diameter (Metric)	10.0 mm
Stud Diameter (Imperial)	0.39
Material	Polyamide 4.6 (PA46)
Material Shortcut	PA46
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +266°F (-40°C to +130°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)