

Specification Sheet

Part Number: 157-00358

1-Piece cable tie and fir tree mount offers a simple method to bundle and fasten cables to panels with thickness up to 6.0 mm.

Robust fir tree design provides low insertion effort yet delivers exceptional retention strength in a 10 mm hole.

8 inch outside serrated tie with low profile head design provides security for bundles up to 50 mm.

25 mm stand off on cable tie creates an alternate solution when an offset fastening option is required directly above the hole away from the mounting panel.



Standoff Fir Tree Cable Tie, 25mm standoff, 9.6 - 10.4 mmHole Dia, 9.5" Tie, PA66HIRHSUV, Black, 3000/ctn

Article Number	157-00358
Type	T50ROSFT1025SO
Color	Black (BK)
Quantity Per	pack

Product Description	Offset Cable Ties route and position wire and cable bundles away from a mounting hole. The offset bar between the fir tree and cable tie strap provides a robust and cored-out design to eliminate any potential bending of the wire or cable assembly once installed. The combination of 12.5 mm and 25 mm offset distances and various fir tree sizes offer coverage for a majority of industry offset routing applications. The outside serrations of the tie strap prevent damage to soft or delicate bundles. One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution.
Short Description	Standoff Fir Tree Cable Tie, 25mm standoff, 9.6 - 10.4 mmHole Dia, 9.5" Tie, PA66HIRHSUV, Black, 3000/ctn
Global Part Name	T50ROSFT1025SO-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	9.5
Length L (Metric)	242.3
Offset Length (Imperial)	0.98
Offset Length (Metric)	25.0
Fixation Method	Fir tree for round holes
Identification Plate Position	none
Releasable Closure	No
Width W (Imperial)	0.44

Width W (Metric)	11.3
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.24
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.38 - 0.41 "
Mounting Hole Diameter D (Metric)	9.6 - 10.4 mm
Mounting Hole Diameter D Min (Imperial)	0.38
Mounting Hole Diameter D Max (Imperial)	0.41
Mounting Hole Diameter D Max (Metric)	10.4
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut	PA66HIRHSUV
Material Cable Tie	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com