

Specification Sheet

Part Number: T120RSM0HIRK2

Covers top of stud for protection from stud end.

Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure.

PA46 material option allows use in high-heat applications.



1-Piece Cable Tie with Stud Mount, 16"L, 0.25" Hole, 120lb Tensile, PA66HIRHSUV, Black, 50/pkg

Article Number	157-01300
Type	T120RSM
Color	Black (BK)
Quantity Per	pack
Product Description	Stud mount tie designed for use on a 1/4" threaded stud or exposed threads of a machine screw.
Short Description	1-Piece Cable Tie with Stud Mount, 16"L, 0.25" Hole, 120lb Tensile, PA66HIRHSUV, Black, 50/pkg
Global Part Name	T120RSM-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)	120
Minimum Tensile Strength (Metric)	535
Length L (Imperial)	16.0
Length L (Metric)	405.0
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.30
Width W (Metric)	7.6
Bundle Diameter Min (Imperial)	0.2
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	3.98
Bundle Diameter Max (Metric)	101.0
Thickness T (Imperial)	0.07
Thickness T (Metric)	1.8

Height H (Imperial)	.77
Height H (Metric)	19.50
Stud Diameter (Metric)	6.3 mm
Stud Diameter (Imperial)	1/4
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)