

## Specification Sheet

Part Number: 3FRP0C



Sheathing allows flexible routing and lead-out of cables

The inner edges are beveled preventing damage to cables

Sheathing is reusable and resistant to most chemicals

Spiralwrap is U.L. Recognized

Spiralwrap Protective Sheathing, 0.5" Diameter, PE-FR, Black, 100 ft/roll

Article Number 161-05048

Type 3FRP

Color Black (BK)

Quantity Per pack

Product Description HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.

Short Description Spiralwrap Protective Sheathing, 0.5" Diameter, PE-FR, Black, 100 ft/roll

Global Part Name 3FRP-PE-FR-BK

Length L (Imperial)	100.0
Length L (Metric)	30.48
Variant	Spiral Binding
Bundle Diameter Min (Imperial)	0.37
Bundle Diameter Min (Metric)	9.52
Bundle Diameter Max (Imperial)	4.02
Bundle Diameter Max (Metric)	102.0
Diameter D (Imperial)	0.5
Diameter D (Metric)	12.7
Nominal Diameter (Imperial)	0.5
Nominal Diameter (Metric)	12.7
Wall Thickness WT (Imperial)	.062
Wall Thickness WT (Metric)	1.57
Material	Polyethylene, flame retardant (PE-FR)
Material Shortcut	PE-FR

Flammability	UL 94 V-2
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-4°F to +176°F (-20°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)