

Specification Sheet

Part Number: 161-64213



Unique open design for easy branch-offs at any point along the harness.

Overwrap formation provides abrasion protection and accommodates multiple bundle configurations.

Flexible construction and design eliminates pinch points and minimizes bending fatigue, making it ideal for applications involving movement and vibration.

Split shape allows for future access without disassembly.

Helawrap, HWPP16, 5/8" (16mm) Dia, PP, Black, 100 ft/reel

Article Number	161-64213
Type	HWPP16
Color	Black (BK)
Quantity Per	pack
Product Description	The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Helawrap easily wraps around cables with a "zipper-like" motion to protect against abrasion and mechanical stress caused by movement and bending. A handy application tool is included in every package for faster installations.
Short Description	Helawrap, HWPP16, 5/8" (16mm) Dia, PP, Black, 100 ft/reel

Global Part Name HWPP16-PP-BK

Length L (Imperial) 100.0

Length L (Metric) 30.48

Variant Spiral Binding

Bundle Diameter Min (Imperial) 0.51

Bundle Diameter Min (Metric) 12.95

Bundle Diameter Max (Imperial) 0.63

Bundle Diameter Max (Metric) 16.0

Diameter D (Imperial) 0.5

Diameter D (Metric) 16.0

Nominal Diameter (Imperial) 0.63

Nominal Diameter (Metric) 16.0

Wall Thickness WT (Imperial) 0.03

Wall Thickness WT (Metric) 0.80

Material Polypropylene (PP)

Material Shortcut	PP
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-76°F to +230°F (-60°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	EDAG ECE R 118-03 Abschnitt 6
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com