

Specification Sheet

Part Number: 1NFP0C



Sheathing allows flexible routing and lead-out of cables.

The inner edges are beveled preventing damage to cables.

Sheathing is reusable and resistant to most chemicals.

Spiralwrap is U.L. Recognized.

Spiralwrap Protective Sheathing, 0.13" Diameter, PE, Black, 100 ft/roll

Article Number	161-05004
Type	1NFP
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.
Short Description	Spiralwrap Protective Sheathing, 0.13" Diameter, PE, Black, 100 ft/roll
Global Part Name	1NFP-PE-BK

Length L (Imperial)	100.0
Length L (Metric)	30.48
Variant	Spiral Binding
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.6
Bundle Diameter Max (Imperial)	0.5
Bundle Diameter Max (Metric)	12.7
Diameter D (Imperial)	0.125
Diameter D (Metric)	3.18
Nominal Diameter (Imperial)	0.13
Nominal Diameter (Metric)	3.18
Wall Thickness WT (Imperial)	0.032
Wall Thickness WT (Metric)	0.81
Material	Polyethylene (PE)
Material Shortcut	PE

Halogen Free	No
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-76°F to +190°F (-60°C to +88°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com