

Specification Sheet

Part Number: 166-90984



Overlapping conduit design increases mechanical protection and eliminates unintentional exposure of wires caused by motion, vibration or when routed around corners.

Material is easy to use and cut - reduces installation time and labor costs.

Good impact strength; recovers quickly if crushed.

HelaGuard Non-Metallic Conduit, Double Slit, 0.50" Dia, PP, Black, 164 ft/Std. Reel

Article Number	166-90984
Type	HG-DC0500
Color	Black (BK)
Quantity Per	pack
Product Description	A standard-weight, polypropylene, corrugated two-piece conduit, each of which is slit open to ease installation and maintenance of wire and cable bundles. The interlocking construction is excellent for retrofitting projects. Polypropylene material is typically used in building construction, particulaly where buried in concrete or plaster. Flexible, abrasion resistant and durable for a variety of applications.
Short Description	HelaGuard Non-Metallic Conduit, Double Slit, 0.50" Dia, PP, Black, 164 ft/Std. Reel

Global Part Name	HG-DC0500-PP-BK
------------------	-----------------

Length L (Imperial)	164.0
---------------------	-------

Length L (Metric)	50
-------------------	----

Inner Diameter D (Imperial)	0.55
-----------------------------	------

Inner Diameter D (Metric)	13.9
---------------------------	------

Outside Diameter OD (Imperial)	0.84
--------------------------------	------

Outside Diameter OD (Metric)	21.2
------------------------------	------

Nominal Diameter (Imperial)	0.5
-----------------------------	-----

Nominal Diameter (Metric)	21
---------------------------	----

Material	Polypropylene (PP)
----------	--------------------

Material Shortcut	PP
-------------------	----

Flammability	EN IEC 61386
--------------	--------------

Halogen Free	No
--------------	----

UV Resistant (Yes/No)	No
-----------------------	----

Use Conditions	For Indoor Use Only
----------------	---------------------

Operating Temperature	-4°F to +194°F (-20°C to +90°C)
-----------------------	---------------------------------

Reach Compliant (Article 33)	Yes
------------------------------	-----

ROHS Compliant	Yes
----------------	-----

Package Quantity (Imperial)	164.0
-----------------------------	-------

Package Quantity (Metric)	50
---------------------------	----

Customs Number	3926909988
----------------	------------

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)