

Specification Sheet

Part Number: CTP380C

Split side is ideal for applications where braided tubing or spiral wrap may be difficult to install.

Tubing provides full coverage where spiral wrap or other coverings may not be suitable.

Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires.



Convoluted Tubing, Slit, 0.38" Dia, PE, Black, 100 ft/ctn

Article Number	169-60545
----------------	-----------

Type	CTP380
------	--------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.
---------------------	--

Short Description	Convuluted Tubing, Slit, 0.38" Dia, PE, Black, 100 ft/ctn
-------------------	---

Global Part Name	CTP380-PE-BK
------------------	--------------

Length L (Imperial)	1500.0
---------------------	--------

Length L (Metric)	457.2
-------------------	-------

Variant	Slit
---------	------

Inner Diameter D (Imperial)	0.380
-----------------------------	-------

Inner Diameter D (Metric)	9.65
---------------------------	------

Diameter D (Imperial)	0.526
-----------------------	-------

Diameter D (Metric)	13.36
---------------------	-------

Outside Diameter OD (Imperial)	0.526
--------------------------------	-------

Outside Diameter OD (Metric)	13.36
------------------------------	-------

Nominal Diameter (Imperial)	0.38
-----------------------------	------

Nominal Diameter (Metric)	9.00
---------------------------	------

Wall Thickness WT (Imperial)	0.005
------------------------------	-------

Wall Thickness WT (Metric)	0.127
----------------------------	-------

Material	Polyethylene (PE)
Material Shortcut	PE
Flammability	Not Flame Retardant
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com