

Specification Sheet

Part Number: CTP580STDUNSLIT

Durable tubing provides protection of wire harness from friction, vibration, fraying and puncture

Tubing protects cables and wires against automotive fluids, vibration wear

Weather resistant material provides protection against water, snow, ice, and the effects of heat, cold, and sunlight

Nylon material is formulated to withstand high temperatures



Convoluted Tubing, Unslit, 0.63" Dia, PE, Black, 700 ft/ctn

Article Number	169-60546
Type	CTP580UNSLIT
Color	Black (BK)
Quantity Per	carton

Product Description	HellermannTyton's Convoluted Tubing, also known as Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.
---------------------	--

Short Description	Convoluted Tubing, Unslit, 0.63" Dia, PE, Black, 700 ft/ctn
-------------------	---

Global Part Name	CTP580UNSLIT-PE-BK
------------------	--------------------

Length L (Imperial)	700.0
---------------------	-------

Length L (Metric)	213.4
-------------------	-------

Variant	Unslit
---------	--------

Inner Diameter D (Imperial)	0.639
-----------------------------	-------

Inner Diameter D (Metric)	16.23
---------------------------	-------

Diameter D (Imperial)	0.837
-----------------------	-------

Diameter D (Metric)	21.26
---------------------	-------

Outside Diameter OD (Imperial)	0.837
--------------------------------	-------

Outside Diameter OD (Metric)	21.26
------------------------------	-------

Nominal Diameter (Imperial)	0.63
-----------------------------	------

Nominal Diameter (Metric)	16.00
---------------------------	-------

Wall Thickness WT (Imperial)	0.005
------------------------------	-------

Wall Thickness WT (Metric)	0.127
----------------------------	-------

Material	Polyethylene (PE)
----------	-------------------

Material Shortcut	PE
Flammability	Not Flame Retardant
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	700
Package Quantity (Metric)	213.36
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com