

## Specification Sheet

Part Number: 170-01163

Self-wrapping woven sleeving made of fiberglass and PET polyester protects against chewing damage.

Provides good protection against abrasion, UV and weathering, vibration and impact.

Quick and easy installation and removal, ideal for retrofitting.

Lightweight material won't add significant weight to the installation.

Resists acids, solvents and micro-organisms for extended performance in industrial environments.



Braided Sleeving, Twist-In Rodent-Repellent Wrap, 29mm Dia. FG/PET, White, 49.2 ft/rl

|                |           |
|----------------|-----------|
| Article Number | 170-01163 |
|----------------|-----------|

|      |                |
|------|----------------|
| Type | Twist-In-RR-29 |
|------|----------------|

|       |                       |
|-------|-----------------------|
| Color | White (WH) Black (BK) |
|-------|-----------------------|

|              |      |
|--------------|------|
| Quantity Per | pack |
|--------------|------|

|                     |                                                                                                                                                                                                                                             |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | Twist-In Rodent-Repellent Wrap is a self-closing fiberglass sleeving used to bundle cables and hoses and protect against rodents in infestation-prone areas such as automotive, railways, telecom, underground and waste treatment systems. |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                                |                                                                                       |
|--------------------------------|---------------------------------------------------------------------------------------|
| Short Description              | Braided Sleeving, Twist-In Rodent-Repellent Wrap, 29mm Dia. FG/PET, White, 49.2 ft/rl |
| Global Part Name               | Twist-In-RR-29-PET/GF-BK/WH                                                           |
| Length L (Metric)              | 15                                                                                    |
| Bundle Diameter Min (Imperial) | 0.98                                                                                  |
| Bundle Diameter Min (Metric)   | 25                                                                                    |
| Bundle Diameter Max (Imperial) | 1.14                                                                                  |
| Bundle Diameter Max (Metric)   | 29                                                                                    |
| Nominal Diameter (Imperial)    | 1.0                                                                                   |
| Nominal Diameter (Metric)      | 25.4                                                                                  |
| Wall Thickness WT (Metric)     | 0.8                                                                                   |
| Material                       | Polyester (PET) Glass Fiber (GF)                                                      |
| Material Shortcut              | GF PET                                                                                |
| Flammability                   | FMVSS 302                                                                             |
| Halogen Free                   | Yes                                                                                   |

|                              |                                   |
|------------------------------|-----------------------------------|
| UV Resistant (Yes/No)        | Yes                               |
| Use Conditions               | For Indoor and Outdoor Use        |
| Operating Temperature        | -94°F to +257°F (-70°C to +125°C) |
| Reach Compliant (Article 33) | Yes                               |
| ROHS Compliant               | Yes                               |
| Certification/Specification  | EN [45545-2]                      |
| Package Quantity (Imperial)  | 49.2                              |
| Package Quantity (Metric)    | 15                                |
| Customs Number               | 7019901100                        |

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: corp@htamericas.com