

Specification Sheet

Part Number: 170-03148



- Flexible construction that conforms to irregular shapes and contours.
- Hook and loop feature wraps over cable bundle allowing future access to cables.
- Easy access saves assembly time and allows for easy splicing or insertion of additional wires.
- PET yarn construction offers excellent protection against cuts and abrasions.

Braided Sleeving, Hook & Loop, 0.5" Dia, PET, Black, 100 ft/bulk reel

Article Number	170-03148
Type	BSHKLP120B
Color	Black (BK)
Quantity Per	pack
Product Description	Designed for the quick and easy management of wires, this expandable sleeving has an internal hook and loop strap that is able to adhere to its outer PET braid, delivering flexibility that allows it to fit around odd-shaped connectors. Its color-matched hook and loop closure provides for an easy on and off installation, as well as instant and convenient access for harness break-outs and networks. the primary application for this sleeving is the wrapping and bunching of cables in a deployed situation or when frequent access to cables is necessary.

Short Description	Braided Sleeving, Hook & Loop, 0.5" Dia, PET, Black, 100 ft/bulk reel
Global Part Name	BSHKLP120B-PET-BK
Length L (Imperial)	100.0
Length L (Metric)	30.48
Bundle Diameter Min (Imperial)	0.1
Bundle Diameter Min (Metric)	2.54
Bundle Diameter Max (Imperial)	0.5
Bundle Diameter Max (Metric)	12.7
Diameter D (Imperial)	0.50
Diameter D (Metric)	12.7
Nominal Diameter (Imperial)	0.5
Nominal Diameter (Metric)	12.7
Wall Thickness WT (Imperial)	0.025
Wall Thickness WT (Metric)	0.635
Material	Polyester (PET)

Material Shortcut	PET
Flammability	UL 94 V-0 FAR 25
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	5808100000

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)