

Specification Sheet

Part Number: 170-03207



Tightly woven fabric bundles and protects cables and hoses from sunlight and abrasion damage; also deflects high pressure hose ruptures.

Nylon material resists gasoline, salt and other chemicals.

Cut to size easily with regular scissors.

Braided Sleeving, Heavy Duty, 3" Dia, PA6, Black, 25 ft/reel

Article Number	170-03207
Type	BSHDWV
Color	Black (BK)
Quantity Per	pack
Product Description	Sleeving made of a tightly woven nylon fabric, slides onto hoses, cables and components to protect them from abrasion and environmental elements, including UV damage. Also protects surrounding surfaces from damage.
Short Description	Braided Sleeving, Heavy Duty, 3" Dia, PA6, Black, 25 ft/reel
Global Part Name	BSHDWV-PA6-BK

Length L (Imperial)	25.0
---------------------	------

Length L (Metric)	7.62
-------------------	------

Bundle Diameter Min (Imperial)	0.1
--------------------------------	-----

Bundle Diameter Min (Metric)	2.54
------------------------------	------

Bundle Diameter Max (Imperial)	3
--------------------------------	---

Bundle Diameter Max (Metric)	76.2
------------------------------	------

Diameter D (Imperial)	3.34
-----------------------	------

Diameter D (Metric)	84.84
---------------------	-------

Nominal Diameter (Imperial)	3
-----------------------------	---

Nominal Diameter (Metric)	76.2
---------------------------	------

Wall Thickness WT (Imperial)	.045
------------------------------	------

Wall Thickness WT (Metric)	1.14
----------------------------	------

Material	Polyamide 6 (PA6)
----------	-------------------

Material Shortcut	PA6
-------------------	-----

Halogen Free	Yes
--------------	-----

UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-49°F to +248°F (-45°C to +120°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	7.62
Customs Number	5806322000

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)