


Specification Sheet

Part Number: 181-13015



- Strong fingers prevent unwanted breaking.
- Restricted opening prevents unintended removal of wires and permits any individual wire to be traced without disconnection.
- Supplied with mounting holes to streamline installation.
- Optional covers enhance protection and appearance.

Slotted Wall Wiring Duct, 1" x 3", Non-Adhesive, PVC, Gray, 7FT, 140 ft/carton

Article Number	181-13015
Type	SL1X3
Color	Gray (GY)
Quantity Per	carton
Product Description	HellermannTyton Slotted Wall Wiring Duct features break-away fingers that provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a greater opening is required. The lower score line allows the sidewall to be smoothly cut for joints and T's.
Short Description	Slotted Wall Wiring Duct, 1" x 3", Non-Adhesive, PVC, Gray, 7FT, 140 ft/carton

Global Part Name	SL1X3-PVC-GY
Length L (Imperial)	7
Length L (Metric)	2.13
Fixation Method	Non-Adhesive
Width W (Imperial)	1.00
Width W (Metric)	25.40
Height H (Imperial)	1.06
Height H (Metric)	26.92
Mounting Hole Centers (Imperial)	4.0
Material	Polyvinylchloride - rigid extrusion grade (PVC)
Material Shortcut	PVC
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	+122°F (+50°C)
Reach Compliant (Article 33)	No

ROHS Compliant	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	140
Package Quantity (Metric)	42.7
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)