

Specification Sheet

Part Number: 183-12525



Excellent fire-safety characteristics.

Narrow slots suitable for small-diameter wires.

Fingers can be removed with no sharp edges at pre-notched snap-off points.

Duct covers hold securely even in a vertical position and under vibration.

Halogen Free Slotted Wiring Duct, without Adhesive, 25mm x 25mm, Piece/ABS, Gray RAL, 48 m/Box

Article Number 183-12525

Type HTWD-HF-25X25

Color Gray RAL 7035 (7035)

Quantity Per pack

Product Description HellermannTyton HTWD-HF halogen-free ducts are used wherever there are high demands on personal or material safety, such as public transport, tunnels, escalators and data processing centers. Snap-on covers are included with corresponding duct sizes to ensure complete wire protection. Base perforation according to DIN EN 50085. Note: Halogen-free PC+ABS is not resistant to all oils and greases.

Short Description Halogen Free Slotted Wiring Duct, without Adhesive, 25mm x 25mm, Piece/ABS, Gray RAL, 48 m/Box

Global Part Name	HTWD-HF-25X25-PC/ABS-GY
Length L (Imperial)	6.56
Length L (Metric)	2
Fixation Method	Screw Mounting
Width W (Imperial)	.98
Width W (Metric)	25
Height H (Imperial)	0.98
Height H (Metric)	25.0
Material	Acrylonitrile Butadiene Styrene alloyed with Polycarbonate (PC/ABS)
Material Shortcut	PC/ABS
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-13°F to +194°F (-25°C to +90°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 62275 EN [45545-2]
UL Recognized (US)	Yes
Package Quantity (Imperial)	157.48
Package Quantity (Metric)	48.0
Customs Number	3925900000

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com