

## Specification Sheet

Part Number: 183-13737



Excellent fire-safety characteristics.

Narrow slots suitable for small-diameter wires.

Fingers can be removed with no sharp edges at pre-notched snap-off points.

Duct covers hold securely even in a vertical position and under vibration.

Halogen Free Slotted Wiring Duct, without Adhesive, 37.5mm x 37.5mm, Piece/ABS, Gray RAL, 40 m/Box

Article Number 183-13737

Type HTWD-HF-37.5X37.5

Color Gray RAL 7035 (7035)

Quantity Per pack

Product Description HellermannTyton HTWD-HF halogen-free ducts are used wherever there are high demands on personal or material safety, such as public transport, tunnels, escalators and data processing centers. Snap-on covers are included with corresponding duct sizes to ensure complete wire protection. Base perforation according to DIN EN 50085. Note: Halogen-free PC+ABS is not resistant to all oils and greases.

Short Description Halogen Free Slotted Wiring Duct, without Adhesive, 37.5mm x 37.5mm, Piece/ABS, Gray RAL, 40 m/Box

|                       |                                                                     |
|-----------------------|---------------------------------------------------------------------|
| Global Part Name      | HTWD-HF-37.5X37.5-PC/ABS-GY                                         |
| Length L (Imperial)   | 6.56                                                                |
| Length L (Metric)     | 2                                                                   |
| Fixation Method       | Screw Mounting                                                      |
| Width W (Imperial)    | 1.48                                                                |
| Width W (Metric)      | 37.5                                                                |
| Height H (Imperial)   | 1.48                                                                |
| Height H (Metric)     | 37.5                                                                |
| Material              | Acrylonitrile Butadiene Styrene alloyed with Polycarbonate (PC/ABS) |
| Material Shortcut     | PC/ABS                                                              |
| Flammability          | UL 94 V-0                                                           |
| Halogen Free          | Yes                                                                 |
| UV Resistant (Yes/No) | No                                                                  |
| Use Conditions        | For Indoor Use Only                                                 |
| Operating Temperature | -13°F to +194°F (-25°C to +90°C)                                    |

|                              |                                 |
|------------------------------|---------------------------------|
| Reach Compliant (Article 33) | Yes                             |
| ROHS Compliant               | Yes                             |
| Certification/Specification  | UL   ANSI/UL 62275 EN [45545-2] |
| UL Recognized (US)           | Yes                             |
| Package Quantity (Imperial)  | 131.23                          |
| Package Quantity (Metric)    | 40                              |
| Customs Number               | 3925900000                      |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com