


Specification Sheet

Part Number: 183-21010



Narrow slots suitable for small-diameter wires.

Fingers can be removed with no sharp edges at pre-notched snap-off points.

Duct covers hold securely even in a vertical position and under vibration.

Base perforation according to DIN EN 50085.

Halogen Free Slotted Wiring Duct & Cover, without Adhesive, 100mm x 100mm, Piece/ABS, Gray, 8 m/Box

Article Number	183-21010
----------------	-----------

Type	HTWD-HF-100X100
------	-----------------

Color	Gray (GY)
-------	-----------

Quantity Per	pack
--------------	------

Product Description	HelaDuct HTWD-HF wiring duct is used to route and protect wires in control panels and switching systems where there are high demands on personal or material safety in case of fire, such as in public transport, tunnels, data processing centers or public buildings. Snap-on covers are included with corresponding duct sizes to ensure complete wire protection.
---------------------	---

Short Description	Halogen Free Slotted Wiring Duct & Cover, without Adhesive, 100mm x 100mm, Piece/ABS, Gray, 8 m/Box
-------------------	---

Global Part Name	HTWD-HF-100X100-PC/ABS-GY
Length L (Imperial)	6.56
Length L (Metric)	2.0
Fixation Method	Screw Mounting
Width W (Imperial)	3.94
Width W (Metric)	100.0
Height H (Imperial)	3.94
Height H (Metric)	100.0
Material	Acrylonitrile Butadiene Styrene alloyed with Polycarbonate (PC/ABS)
Material Shortcut	PC/ABS
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-13°F to +194°F (-25°C to +90°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL csa-C22.2 no. 62275 UL csa-C22.2 no. 18.5 UL ANSI/UL 1565 UL ANSI/UL 62275 EN [45545-2]
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	26.25
Package Quantity (Metric)	8.0
Customs Number	3925900000

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com