


Specification Sheet

Part Number: 184-33005



Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.

Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.

Mounting holes are uniform in size and are offered every 2 inches to accommodate compact designs and ease installation.

Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.

High Density Slotted Wall Wiring Duct, 3" x 3", Non-Adhesive, PVC, Gray, 7FT, 140ft/Carton

Article Number	184-33005
Type	SLHD3X3
Color	Gray (GY)
Quantity Per	carton
Product Description	HellermannTyton High-Density Slotted Wall Wiring Duct features narrow fingers equaling a 2-to-1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.

Short Description	High Density Slotted Wall Wiring Duct, 3" x 3", Non-Adhesive, PVC, Gray, 7FT, 140ft/Carton
Global Part Name	SLHD3X3-PVC-GY
Length L (Imperial)	7
Length L (Metric)	2.13
Width W (Imperial)	3.00
Width W (Metric)	76.20
Height H (Imperial)	3.07
Height H (Metric)	77.90
Mounting Hole Centers (Imperial)	2.00
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	+122°F (+50°C)

Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	CSA EN 50085-2-3_1A UL EN 50085-1:2005 + A1:2013
UL Recognized (US)	Yes
Package Quantity (Imperial)	120.0
Package Quantity (Metric)	36.58
Customs Number	3925900000

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)