

Specification Sheet

Part Number: ASNP24-70



The ASNP tools offer particular advantages in series production.

By means of an attachment screw, the draw-in area can be limited, by which an overstretching of the snapper is prevented.

Mechanical Vertical Snapper Hose Clamp Tool for Snappers 24-70, 1/pkg

Article Number	191-24700
----------------	-----------

Type	ASNP24-70
------	-----------

Color	Red (RD)
-------	----------

Quantity Per	pack
--------------	------

Product Description	The ASNP snapper tools offer a highly efficient method of installing Snapper clips. The ASNP tools offer particular advantages in series production. By means of an adjustable screw, the 'close-down' area can be controlled avoiding damaging either the clip or the hose.
---------------------	--

Short Description	Mechanical Vertical Snapper Hose Clamp Tool for Snappers 24-70, 1/pkg
-------------------	---

Global Part Name	ASNP24-70-MET/PL-RD
------------------	---------------------

Tension Setting Tools	Manual
Material	Plastic (PL) Metal (MET)
Material Shortcut	MET PL
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8203206060