

Specification Sheet

Part Number: D15L4



Available in three sizes, HellermannTyton screw mount clips offer quick, snap-in action.

These clips allow for easy release for wiring changes or replacements, saving both time and money.

Article Number	211-70203
Type	8D15
Color	Black (BK)
Quantity Per	pack
Product Description	Developed for fixing pipes, cables and hoses, the D-Clips elastic locking system ensures optimal fixing and at the same time, easy removal of the fixed elements by simply pressing the lower latch down and pulling the fixed element.
Short Description	Screw Mount Cable Clip, 0.59" Max Bundle Dia, 0.31" Mounting Hole Dia, POM, Black, 200/pkg
Global Part Name	8D15-POM-BK

Length L (Imperial)	0.98
Length L (Metric)	25.0
Fixation Method	screw-hole
Variant	Closed
Width W (Imperial)	0.59
Width W (Metric)	15.0
Bundle Diameter Min (Imperial)	0.59
Bundle Diameter Min (Metric)	15.0
Bundle Diameter Max (Imperial)	0.59
Bundle Diameter Max (Metric)	15.0
Nominal Diameter (Imperial)	1.56
Nominal Diameter (Metric)	15.0
Wall Thickness WT (Imperial)	0.08
Wall Thickness WT (Metric)	2.0
Mounting Hole Diameter D (Imperial)	0.31 "
Mounting Hole Diameter D (Metric)	8.0 mm

Mounting Hole Diameter D Max (Metric) 8.0

Material Polyacetal (POM)

Material Shortcut POM

Flammability UL 94 HB

UV Resistant (Yes/No) No

Operating Temperature -40°F to +194°F (-40°C to +90°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 200

Package Quantity (Metric) 200

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)