

Specification Sheet

Part Number: 211-00264



P-Clamps easily guide and locate wire and cables up to 1" in diameter.
Designed with a radius edge to prevent chafing and cutting into insulation.

P-Clamp, 0.39" Wide, 0.26" Max Bundle Dia, 0.17" Mounting Hole Dia, PA66, Natural, 100/pkg

Article Number	211-00264
Type	H3P
Color	Natural (NA)
Quantity Per	pack
Product Description	HellermannTyton P-Clamps easily guide and locate wires and cables. The clamps are designed with a radius edges to prevent chafing and cutting into insulation. Available sizes up to 1" bundle diameters.
Short Description	P-Clamp, 0.39" Wide, 0.26" Max Bundle Dia, 0.17" Mounting Hole Dia, PA66, Natural, 100/pkg
Global Part Name	H3P-PA66-NA

Fixation Method	screw-hole
Variant	Closed
Width W (Imperial)	0.39
Width W (Metric)	10.0
Bundle Diameter Max (Imperial)	0.26
Bundle Diameter Max (Metric)	6.5
Nominal Diameter (Imperial)	0.25
Nominal Diameter (Metric)	6.5
Wall Thickness WT (Imperial)	0.039
Wall Thickness WT (Metric)	1.0
Mounting Hole Diameter D (Imperial)	0.17 "
Mounting Hole Diameter D (Metric)	4.2 mm
Mounting Hole Diameter D Max (Metric)	4.2
Mounting Hole Centers (Imperial)	0.39
Material	Polyamide 6.6 (PA66)

Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)