

## Specification Sheet

Part Number: TSRPFW-JB1

Pre-scored knockouts on the base and all four sides remove easily to accomodate all HellermannTyton TSR/TSRP raceway sizes.

Simple two-piece design is easy to install and includes foam tape backing with rubber based adhesive to assist with temporary positioning and mounting.

Accommodates a variety of alarm/detector and fixture makes and models.

PVC construction is lightweight and durable.

Covers are designed to overlap raceway mating points to hide uneven cuts.

Fittings incorporate a minimum 1" bend radius per TIA/EIA 568-B and 569-A standards.

UL 5A Listed to 600V and CSA Certified to 300V (not to exceed 10 lbs. per UL and 5 lbs. per CSA.)



Single Gang Junction Box, 1-1/4" Deep, PVC, Office White, 1/bg

|                |                     |
|----------------|---------------------|
| Article Number | 250-60001           |
| Type           | TSRP-JB1            |
| Color          | Office White (OEWH) |
| Quantity Per   | pack                |

|                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | Offered in a dual or single gang format, HellermannTyton's low voltage junction boxes are versatile enough for any network cabling application. Available in varying depths, these boxes are all equipped with concentric knockouts on all four sides for every TSR size of raceway, which eliminates routing and installation inconvenience. All five styles of junction boxes come with adhesive strips for the back of the base, and also #6 screws to secure the box to the base. |
| Short Description   | Single Gang Junction Box, 1-1/4" Deep, PVC, Office White, 1/bg                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Global Part Name    | TSRP-JB1-PVC-WH                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| Length L (Imperial) | 4.75                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Length L (Metric)   | 120.65                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| Width W (Imperial)  | 3.0                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Width W (Metric)    | 76.2                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Height H (Imperial) | 1.25                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Height H (Metric)   | 31.75                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Material            | Polyvinylchloride (PVC)                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Material Shortcut   | PVC                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Flammability        | UL 94 V-0                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Halogen Free        | No                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |

|                              |                     |
|------------------------------|---------------------|
| UV Resistant (Yes/No)        | No                  |
| Use Conditions               | For Indoor Use Only |
| Operating Temperature        | +122°F (+50°C)      |
| Reach Compliant (Article 33) | No                  |
| ROHS Compliant               | Yes                 |
| UL Listed (US and Canada)    | Yes                 |
| UL Listed (US)               | Yes                 |
| Package Quantity (Imperial)  | 1                   |
| Package Quantity (Metric)    | 1                   |
| Customs Number               | 3925900000          |

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: corp@htamericas.com