

Specification Sheet

Part Number: TSRPI-JB2

Pre-scored knockouts on the base and all four sides remove easily to accomodate all HellermannTyton TSR/TSRP raceway sizes.

Simple two-piece design is easy to install and includes foam tape backing with rubber based adhesive to assist with temporary positioning and mounting.

Accommodates a variety of alarm/detector and fixture makes and models.

PVC construction is lightweight and durable.

Covers are designed to overlap raceway mating points to hide uneven cuts.

Fittings incorporate a minimum 1" bend radius per TIA/EIA 568-B and 569-A standards.

UL 5A Listed to 600V and CSA Certified to 300V (not to exceed 10 lbs. per UL and 5 lbs. per CSA.)



Single Gang Junction Box, 2.0" Deep, PVC, Ivory, 1/bg

Article Number	250-60005
Type	TSRP-JB2
Color	Ivory (IV)
Quantity Per	pack

Product Description	Offered in a dual or single gang format, HellermannTyton's low voltage junction boxes are versatile enough for any network cabling application. Available in varying depths, these boxes are all equipped with concentric knockouts on all four sides for every TSR size of raceway, which eliminates routing and installation inconvenience. All five styles of junction boxes come with adhesive strips for the back of the base, and also #6 screws to secure the box to the base.
Short Description	Single Gang Junction Box, 2.0" Deep, PVC, Ivory, 1/bg
Global Part Name	TSRP-JB2-PVC-BGE
Length L (Imperial)	4.75
Length L (Metric)	120.65
Width W (Imperial)	3.0
Width W (Metric)	76.2
Height H (Imperial)	2.0
Height H (Metric)	50.80
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Flammability	UL 94 V-0
Halogen Free	No

UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	+122°F (+50°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	3925900000

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)