

Specification Sheet

Part Number: TSRP2W-14

Tamper resistant covers with hidden latch provide security while allowing quick entry for cable maintenance.

PVC construction is lightweight, durable and more affordable than metallic raceway systems.

Flexible hinge designed to reduce stress cracking and discoloration from repeated opening and closing.

Systems and fittings are available in white, office white and ivory to coordinate with a variety of décor.

Fittings incorporate a minimum 1" bend radius to meet TIA/EIA 568-B and 569-A standards.

Enhanced "channel and lug" mating design provides a tighter, more secure fit between raceway lengths and fittings.

System is UL Listed for power up to 600 volts and meet UL5A and CSA 22.2.



Splice Cover, 1-1/4", PVC, 3-Piece, White, 10 Individual/bg

Article Number	250-62142
----------------	-----------

Type	TSRP2-14
------	----------

Color	White (WH)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton surface raceway systems are the ideal solution for routing communication and power cables. No need to break into existing walls - raceway systems are designed to route cable along wall surfaces. Made of a PVC material, components are durable and affordable; and the one piece construction and adhesive tape backing make positioning and mounting easy. HellermannTyton offers a low voltage TSR system and a power rated TSRP system that are available in three different diameters to accommodate different cable and wire bundle and conduit sizes. Both systems include a complete line of fittings and junction boxes that allow for clean and professional installations. TSRP surface raceway systems are designed to aesthetically organize and route either power or communications cables.
Short Description	Splice Cover, 1-1/4", PVC, 3-Piece, White, 10 Individual/bg
Global Part Name	TSRP2-14-PVC-WH
Length L (Imperial)	2
Length L (Metric)	50.8
Width W (Imperial)	1.479
Width W (Metric)	37.57
Height H (Imperial)	0.825
Height H (Metric)	20.96
Wall Thickness WT (Imperial)	0.09
Wall Thickness WT (Metric)	2.29

Material	Polyvinylchloride (PVC)
----------	-------------------------

Material Shortcut	PVC
-------------------	-----

Flammability	UL 94 V-0
--------------	-----------

Halogen Free	No
--------------	----

UV Resistant (Yes/No)	No
-----------------------	----

Use Conditions	For Indoor Use Only
----------------	---------------------

Operating Temperature	+122°F (+50°C)
-----------------------	----------------

Reach Compliant (Article 33)	No
------------------------------	----

ROHS Compliant	Yes
----------------	-----

UL Listed (US and Canada)	Yes
---------------------------	-----

UL Listed (US)	Yes
----------------	-----

Package Quantity (Imperial)	10
-----------------------------	----

Package Quantity (Metric)	10
---------------------------	----

Customs Number	3925900000
----------------	------------

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)