

Specification Sheet

Part Number: TT822OUTSM

Clean Start ribbons prolong printhead life, while reducing maintenance costs.

Ribbons are resin based for the best print durability.

Ribbons are available to fit all HellermannTyton printers for easy resupply.

Ribbons meet UL recognition and Military standard where applicable to meet specific industry label requirements.



Clean Start Thermal Transfer Ribbon, Hard Resin, 4.33" x 242', 0.5" Core, PET, Black, 1/pkg

Article Number

556-00145

Type

TT822OUTSM

Color

Black (BK)

Quantity Per

pack

Product Description

HellermannTyton Clean Start thermal transfer ribbons incorporate an innovative, patented printhead cleaner built right into the ribbon. Clean Start ribbon removes debris before it builds up on the printhead, extending printer life. Available on 1/2" and 1" cores, the ribbons are coated side out and available in two different lengths. All ribbons are available in a variety of colors and are matched to the HellermannTyton label stock to give the best chemical and abrasion resistance.

Short Description	Clean Start Thermal Transfer Ribbon, Hard Resin, 4.33" x 242', 0.5" Core, PET, Black, 1/pkg
Global Part Name	TT822OUTSM-PET-BK
Length L (Imperial)	242.0
Length L (Metric)	74
Variant	Colored ribbon
Width W (Imperial)	4.33
Width W (Metric)	110.0
Material	Polyester Film (PET)
Material Shortcut	PET
Halogen Free	No
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	+40°F to +300°F (+4°C to +82°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	3702440160

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)