

Specification Sheet

Part Number: 556-26006



Halogen free for low-smoke and low-fire hazard applications.

White front and yellow back for versatility.

Superior strength and tear resistance for long lasting identification.

Pre-cut slots to secure the TipTags using HellermannTyton cable ties.

TipTag, 2.59 x .50", PO/Polyester, White/Yellow, 500/roll

Article Number	556-26006
Type	TIPTAGVA10X65YEW
Color	White (WH) Yellow (YE)
Quantity Per	pack
Product Description	TIPTAGs are halogen free, tear resistant, and lightweight cross laminated polyolefin tags ideal for use where weight is a critical factor. Each side is a different color. One side is yellow and the other side is White so that a high contrast black on yellow or black on white mark can be printed.
Short Description	TipTag, 2.59 x .50", PO/Polyester, White/Yellow, 500/roll
Global Part Name	TIPTAGVA10X65YEW-PO-WH/YE

Length L (Imperial)	0.5
Length L (Metric)	12.7
Fixation Method	Others
Variant	Other
Width W (Imperial)	2.59
Width W (Metric)	65.0
Height H (Imperial)	0.5
Height H (Metric)	12.7
Cable Tie Width Max (Imperial)	0.25
Cable Tie Width Max (Metric)	6.35
Material	Polyolefin (PO)
Material Shortcut	PO
US MIL SPEC	MIL-STD-202G Method 215K SAE-AS81531
Halogen Free	Yes

UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-58°F to +221°F (-50°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	MIL-STD-202G Method 215K BS-4G-198-3, Type 11a SAE - AS81531
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3920990000

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)