

Specification Sheet

Part Number: 556-83013

TAGLF is a limited fire hazard Tiptag that can be used in confined spaces where fire is a concern.

Halogen free so that it will not release toxic fumes if exposed to fire.

TAGLF is a low-smoke, low fire hazard product for use in any confined space where cable identification is critical.

Product Image

Tiptag, Halogen Free, 10mm x 51mm, 4 holes, White, 2000 per roll

Article Number 556-83013

Type TAGLF10X51-4

Color White (WH)

Quantity Per pack

Product Description TAGLF is a Tiptag that is designed for confined spaces, such as rail cars, where a low smoke, low fire hazard marker is required. The TAGLF is Halogen free and will not release harmful fumes when burned.

Short Description Tiptag, Halogen Free, 10mm x 51mm, 4 holes, White, 2000 per roll

Global Part Name TAGLF10X51-4-PO-X-WH

Length L (Imperial) 2.0

Length L (Metric)	51.5
Fixation Method	Others
Variant	Roller form
Width W (Imperial)	0.39
Width W (Metric)	10.4
Height H (Imperial)	0.39
Width of Liner (Metric)	90.0
Width of Liner (Imperial)	3.50
Cable Tie Width Max (Metric)	4.6
Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
Flammability	ASTM D635
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only

Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	SAE - AS81531 ASTM 1354 ASTM E 662 ASTM E 162 MIL-STD-202G Method 215K EN [45545-2]
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3920990000
Labels per Column	1

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com